DISINFECTION GATE SPANNER SK

FAST AND EFFECTIVE DISINFECTION OF PEOPLE





DISINFECTION GATE SPANNER SK



PREVENTION FROM VIRUSES AND BACTERIA

We are aware of the value of human health and the importance of preventive measures in the current situation but mostly from long-term perspective. We bring to the market an innovative solution designed for contactless disinfection of people.

Disinfection gates Spanner SK with built-in contactless height sensors use nozzles to disperse the disinfectant in the form of a fine mist on people passing through these gates.

They are made of stainless steel and can be installed in front of entrances to buildings, offices, manufacturing plants, retail chains, medical or various other facilities, simply wherever is necessary to disinfect a large number of people in a short time.

Thanks to a specific disinfectant, they can be installed outdoors or indoors.

The Disinfection gate does not guarantee perfect virus protection. It is a way of reducing the risk of spread of the infection.











DESCRIPTION OF THE DISINFECTION GATE



FAST AND EFFECTIVE DISINFECTION

The passes through the disinfection gate have a width 800 mm.

After entering the disinfection area, height sensors activate a disinfection process automatically. During this process disinfectant is applied on the person in the gate area by using 8 nozzles. The upper sensor switches the upper row of 4 nozzles separately and the lower sensor switches the lower row of 4 nozzles separately (according to body height), while the head of the disinfected person is not directly affected by the disinfectant.

People enter the area of the gate individually and stay here for a few seconds, depending on the timer settings. After finishing the process of disinfection, person leave the gate area and the disinfection process is completed.

A separate nozzle for hand disinfection is integrated in the gate area.

People enter the gate area individually.

Designed for people over 110 cm. Use by children only under adult supervision.

HOW TO USE DISINFECTION GATE SPANNER SK?



FULLY AUTOMATED SOLUTION

- Enter the disinfection gate area if it is empty
- The disinfection process starts automatically
- Put your hands under the hand disinfection nozzle
- The light signal shows the ongoing disinfection process
- The disinfection process is completed after 5 seconds
- Leave the disinfection gate area







BENEFITS OF THE SPANNER SK DISINFECTION GATE





Source: Spanner SK / ODKAZ NA VIDEO - YouTube/

MAIN CHARACTERISTICS

SPANNER SK
partnerschaftlich in die Zukunft


- MADE OF STAINLESS STEEL
- OPTIMAL DISINFECTION DOSAGE
- CONTACTLESS HEIGHT SENSORS
- 8 NOZZLES FOR FAST APPLICATION OF DISINFECTANT
- 1 SEPARATE HAND DISINFECTION NOZZLE
- SIGNALIZING THE NEED FOR DISINFECTANT
- OUTDOOR OR INDOOR LOCATION
- POSSIBILITY OF A BARRIER-FREE VARIANT
- POSSIBILITY OF INDIVIDUALIZATION / CUSTOMIZATION
- CE CERTIFICATION














WE BUILD A NEW HYGIENE STANDARDS TOGETHER







TECHNICAL SPECIFICATION

Brand:	Spanner SK
Name:	Disinfection Gate
Type:	SP001
Material, sheathing:	Stainless Steel
Dimensions including steps/ramps (hxwxd):	1800 x 1500 x 1800/3150 mm
Step height:	100 mm
Entry width:	800 mm
Supply voltage:	230 V / 50 Hz
Max. input power:	150 W
Power:	0,15 kW
IP protection:	65/20
Operating pressure:	6 bar
Noise emissions:	< 70 dB
Dispenser for disinfection:	281
Disinfection consumption *:	0,11-0,14 l/min
Disinfection liquid:	biocidal, ethanol-free (supplied by Spanner SK)
Max. load:	250 kg
Product weight including steps/ramps:	180 / 200 kg

^{*}Disinfection consumption is indicative and may vary depending on usage.







REFERENCES





The Hotel Park Inn Bratislava



The Hospital in Považská Bystrica

REFERENCES





Matador Dubnica nad Váhom



SHP Harmanec



CONTACTS

PRODUCER:

Spanner SK, k.s. Robotnicka 4352 017 01 Povazska Bystrica **SLOVAKIA**

www.spanner.sk www.disinfectiongate.eu











partnerschaftlich in die Zukunft